

## ARVO X3

Measurment		Filter					
Fluorescence	Excitation <sup>※1</sup>	355/40nm	485/14nm				
	Emission <sup>※2</sup>	460/25nm	535/25nm				
Absorbance		260/10nm	280/10nm	405/10nm	450/8nm	492/8nm	595/10nm
Luminescence		All	460/25nm - 535/25nm (BRET)				

※1 The filters (405/10nm, 450/8nm, 492/8nm and 595/10nm) are also installed but may require additional adjustments.

※2 The filters (410/80nm and 515/30nm) are also installed but may require additional adjustments.